


Connection with ASYG14KMCC and R410A multi OU

When ASYG14KMCC is connected with R410A multi OU, adapter H should be attached with gas pipe. 12.7mm pipe should be used.

Adapter H

Nut side $\phi 9.52$




Pipe side $\phi 12.7$

Connected Pipe for R410A model

14kBTu class : Gas 12.7mm / Liquid 6/35mm


Example using Adapter H for OU (Current R410A multi)

5 room mult OU (AOYG36LBLA5) + 3 x 14kBTu IU



Connection with ASYG14KMCC and R410A multi OU

Attached Adapter H with IU



5 room mult OU (AOYG36LBLA5) + 3 x ASYG14KMCC

